

EU Declaration of Conformity (DoC)

We:

Company Name: AutomationDirect.com
Postal address: 3505 Hutchinson Road
City: Cumming
State: Georgia
Postal Code: 30040
Telephone: (800) 633-0405

declare that the DoC is issued under sole responsibility that the products:

Product Description: Konnect-it terminal block accessories: Marking Tags

(Refer to page 2 of declaration for products covered)

comply with the essential safety requirements and restrictions of the following European Directives:

Low Voltage Directive 2014/35/EU – RoHS Directive 2015/863 EU

Conformity with the provisions of this directive is proved by compliance with the following standards:

EN 60068-2-70: 1996-01

EN IEC 63000:2018-12

We hereby declare that, above product types meet with the essential safety requirements and restrictions mentioned in the EU Directives 2014/35/EU and 2015/863/EU.

Signed for and on behalf of:

AutomationDirect.com

2026-01-23

Héctor Calcaño, Product Engineer,



Place of issue

yyyy-mm-dd

Name, function, signature

Konnect-it part numbers covered by this EU Declaration of Conformity:

Automation Direct P/N				
KN-L5-1	KN-L5-I	KN-L6X-BLNK	KN-LP25-71-80	KN-LRNG2P5-61-70
KN-L5-10	KN-L5-J	KN-MA-1	KN-LP25-BLNK	KN-LRNG2P5-71-80
KN-L5-101-150	KN-L5-K	KN-MA-2	KN-LP4-1-10	KN-LRNG2P5-BLNK
KN-L5-1-10	KN-L5-L	KN-MA-3	KN-LP4-11-20	KN-LRNG6-1-10
KN-L5-11-20	KN-L5-L1	KN-MA-4	KN-LP4-21-30	KN-LRNG6-11-20
KN-L5-1-50	KN-L5-L2	KN-MA-5	KN-LP4-31-40	KN-LRNG6-21-30
KN-L5-151-200	KN-L5-L3	KN-TC-1	KN-LP4-41-50	KN-LRNG6-31-40
KN-L5-2	KN-L5-M	KN-TC-1S	KN-LP4-51-60	KN-LRNG6-41-50
KN-L5-201-250	KN-L5-N	KN-TC-2	KN-LP4-61-70	KN-LRNG6-51-60
KN-L5-21-30	KN-L5-NEG	KN-TC-2S	KN-LP4-71-80	KN-LRNG6-61-70
KN-L5-251-300	KN-L5-O	KN-LFRK10-1-10	KN-LP4-BLNK	KN-LRNG6-71-80
KN-L5-3	KN-L5-P	KN-LFRK10-11-20	KN-LP6-1-10	KN-LRNG6-BLNK
KN-L5-301-350	KN-L5-POS	KN-LFRK10-21-30	KN-LP6-11-20	
KN-L5-31-40	KN-L5-Q	KN-LFRK10-31-40	KN-LP6-21-30	
KN-L5-351-400	KN-L5-R	KN-LFRK10-41-50	KN-LP6-31-40	
KN-L5-4	KN-L5-S	KN-LFRK10-51-60	KN-LP6-41-50	
KN-L5-401-450	KN-L5-T	KN-LFRK10-61-70	KN-LP6-51-60	
KN-L5-41-50	KN-L5-U	KN-LFRK10-71-80	KN-LP6-61-70	
KN-L5-451-500	KN-L5-V	KN-LFRK10-BLNK	KN-LP6-71-80	
KN-L5-5	KN-L5-W	KN-LP1-1-10	KN-LP6-BLNK	
KN-L5-51-100	KN-L5-X	KN-LP1-11-20	KN-LRNG25-1-10	
KN-L5-6	KN-L5X-BLNK	KN-LP1-21-30	KN-LRNG25-11-20	
KN-L5-7	KN-L5-Y	KN-LP1-31-40	KN-LRNG25-21-30	
KN-L5-8	KN-L5-Z	KN-LP1-41-50	KN-LRNG25-31-40	
KN-L5-9	KN-L6P5-1-10	KN-LP1-51-60	KN-LRNG25-41-50	
KN-L5-A	KN-L6P5-11-20	KN-LP1-61-70	KN-LRNG25-51-60	
KN-L5-B	KN-L6P5-21-30	KN-LP1-71-80	KN-LRNG25-61-70	
KN-L5-BLANK	KN-L6P5-31-40	KN-LP1-BLNK	KN-LRNG25-71-80	
KN-L5-C	KN-L6P5-41-50	KN-LP25-1-10	KN-LRNG25-BLNK	
KN-L5-D	KN-L6P5-51-60	KN-LP25-11-20	KN-LRNG2P5-1-10	
KN-L5-E	KN-L6P5-61-70	KN-LP25-21-30	KN-LRNG2P5-11-20	
KN-L5-F	KN-L6P5-71-80	KN-LP25-31-40	KN-LRNG2P5-21-30	
KN-L5-G	KN-L6P5-81-90	KN-LP25-41-50	KN-LRNG2P5-31-40	
KN-L5-GND	KN-L6P5-91-100	KN-LP25-51-60	KN-LRNG2P5-41-50	
KN-L5-H	KN-L6P5-BLNK	KN-LP25-61-70	KN-LRNG2P5-51-60	