



**ROHS CERTIFICATE OF COMPLIANCE**

**DIRECTIVE 2011/65/EU Amendment (EU) 2015/863 and REACH Regulation**

**Restriction of Hazardous Substances**

TE WIRE & CABLE hereby declares and certifies that the subject Product(s) listed below are RoHS compliant according to the definitions and restrictions given for the Directive 2011/65/EU and as amended 2015/863 (June 4, 2015) adding 4 new phthalates to the list of restricted substances in Annex II. These substances, DEHP, BBP, DBP and DIPB will be restricted in the use of electrical and electronic equipment (EEE) in concentrations greater than 0.1% by weight in the homogeneous material effective July 22, 2019.

Automationdirect.com Inc. the following Parts purchased from TE Wire & Cable

<b>ADC Part Number</b>	<b>Description</b>	<b>TE Wire &amp; Cable P/N</b>
THMWK-20-1U-P-1	THCPL Cable; KX Type; 20 AWG; PVC/PVC	P/P-20-KX
THMWJ-20-1U-P-1	THCPL Cable; JX Type; 20 AWG; PVC/PVC	P/P-20-JX
THMWT-20-1U-P-1	THCPL Cable; TX Type; 20 AWG; PVC/PVC	P/P-20-TX
THMWK-20-1U-G-1	THCPL Cable; K Type; 20 AWG; G/G Fiberglass	G/G-20-K
THMWJ-20-1U-G-1	THCPL Cable; J Type; 20 AWG; G/G Fiberglass	G/G-20-J
THMWT-20-1U-G-1	THCPL Cable; TT Type; 20 AWG; G/G Fiberglass	G/G-20-TT
THMWK-20-1S-P-1	THCPL Cable; KX Type; 20 AWG; PVC/PVC. Shld. PLTC	UP/ALPTW-20-KX
THMWJ-20-1S-P-1	THCPL Cable; JX Type; 20 AWG; PVC/PVC. Shld. PLTC	UP/ALPTW-20-JX
THMWT-20-1S-P-1	THCPL Cable; TX Type; 20 AWG; PVC/PVC. Shld. PLTC	UP/ALPTW-20-TX
RTDW-22-1U-P-1	RTD Cable; 22 AWG; PVC/PVC	P/PTW-22F-3SNCU W2R/W
RTDW-24-1S-F-1	RTD Cable; 24 AWG; FEP/FEP; Shld.	TEX/ALTEXTW-24F-3SNCU W2R/W
THMWK-20-2S-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 2 PR OAS PLTC	UP/ALPTWK-02-20-KX
THMWK-20-4S-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 4 PR OAS PLTC	UP/ALPTWK-04-20-KX
THMWK-20-8S-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 8 PR OAS PLTC	UP/ALPTWK-08-20-KX
THMWJ-20-2S-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 2 PR OAS PLTC	UP/ALPTWK-02-20-JX
THMWJ-20-4S-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 4 PR OAS PLTC	UP/ALPTWK-04-20-JX
THMWJ-20-8S-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 8 PR OAS PLTC	UP/ALPTWK-08-20-JX
THMWK-20-2SS-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 2 PR SPOS PLTC	UP/ALM/ALPTWK-02-20-KX
THMWK-20-4SS-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 4 PR SPOS PLTC	UP/ALM/ALPTWK-04-20-KX
THMWK-20-8SS-P-1	THCPL Cable; KX Type; 20 AWG; PVC; 8 PR SPOS PLTC	UP/ALM/ALPTWK-08-20-KX
THMWJ-20-2SS-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 2 PR SPOS PLTC	UP/ALM/ALPTWK-02-20-JX
THMWJ-20-4SS-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 4 PR SPOS PLTC	UP/ALM/ALPTWK-04-20-JX
THMWJ-20-8SS-P-1	THCPL Cable; JX Type; 20 AWG; PVC; 8 PR SPOS PLTC	UP/ALM/ALPTWK-08-20-JX



**TE Wire & Cable**  
The most trusted name in thermocouple wire since 1941

107 North Fifth Street • Saddle Brook, NJ 07663-6167 • 888-4TE-WIRE • [www.tewire.com](http://www.tewire.com)

TE WIRE & CABLE hereby states that the following banned substances do not exceed the threshold level listed, other than exemptions per Annex III approved by the European Commission. Any exemptions are listed below.

Substances	Maximum Limit (%)
Cadmium (Cd)	0.01%
Lead (Pb)	0.10%
Mercury (Hg)	0.10%
Hexavalent chromium (Cr6+)	0.10%
Polybrominated biphenyls (PBB)	0.10%
Polybrominated diphenyl ethers (PBDE)	0.10%
Bis(2-ethylhexyl) phthalate (DEHP)	0.10%
Butyl benzyl phthalate (BBP)	0.10%
Dibutyl phthalate (DBP)	0.10%
Diisobutyl phthalate (DIBP)	0.10%

*Clement Obanya*

Clement Obanya

Quality Engineer

1/13/2020

Signature

Printed Name

Title

Date