

NITRA C-series Cylinder Cross Reference

Short Description of Part Number	NITRA Part #	Bimba Part #	Chicago Cylinder Part #	Fabco-Air Part #	Ingersoll Rand Part #	Norgren Part #	Numatics Part #
COMPACT CYLINDER, 9/16 BORE, 1/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C090025D	FO-020.25				FP056x0.250-SCB	
COMPACT CYLINDER, 9/16 BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C09005D	FO-020.5				FP056x0.500-SCB	
COMPACT CYLINDER, 3/4 BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C12005D	FO-040.5	BRPSR-075-0.500-4	PSD2-0.500	SCC07-J-004	FP075x0.500-SCB	NBSD2-CD00I-AA
COMPACT CYLINDER, 3/4 BORE, 3/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C120075D	FO-040.75	BRPSR-075-0.750-4	PSD2-0.750	SCC07-J-006	FP075x0.750-SCB	NBSD2-CD00M-AA
COMPACT CYLINDER, 3/4 BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C12010D	FO-041	BRPSR-075-1.000-4	PSD2-1.000	SCC07-J-010	FP075x1.000-SCB	NBSD2-CD01A-AA
COMPACT CYLINDER, 3/4 BORE, 1-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C12015D	FO-041.5	BRPSR-075-1.500-4	PSD2-1.500	SCC07-J-014	FP075x1.500-SCB	NBSD2-CD01I-AA
COMPACT CYLINDER, 1-1/16 BORE, 1/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C170025D	FO-090.25	BRPSR-106-0.250-4	PSD3-0.250	SCC11-J-002	FP106x0.250-SCB	NBSD3-CD00E-AA
COMPACT CYLINDER, 1-1/16 BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17005D	FO-090.5	BRPSR-106-0.500-4	PSD3-0.500	SCC11-J-004	FP106x0.500-SCB	NBSD3-CD00I-AA
COMPACT CYLINDER, 1-1/16 BORE, 3/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C170075D	FO-090.75	BRPSR-106-0.750-4	PSD3-0.750	SCC11-J-006	FP106x0.750-SCB	NBSD3-CD00M-AA
COMPACT CYLINDER, 1-1/16 BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17010D	FO-091	BRPSR-106-1.000-4	PSD3-1.000	SCC11-J-010	FP106x1.000-SCB	NBSD3-CD01A-AA
COMPACT CYLINDER, 1-1/16 BORE, 1-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17015D	FO-091.5	BRPSR-106-1.500-4	PSD3-1.500	SCC11-J-014	FP106x1.500-SCB	NBSD3-CD01I-AA
COMPACT CYLINDER, 1-1/16 BORE, 2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17020D	FO-092	BRPSR-106-2.000-4	PSD3-2.000	SCC11-J-020	FP106x2.000-SCB	NBSD3-CD02A-AA
COMPACT CYLINDER, 1-1/16 BORE, 2-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17025D	FO-092.5	BRPSR-106-2.500-4	PSD3-2.500	SCC11-J-024	FP106x2.500-SCB	NBSD3-CD02I-AA
COMPACT CYLINDER, 1-1/16 BORE, 3 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C17030D	FO-093	BRPSR-106-3.000-4	PSD3-3.000	SCC11-J-030	FP106x3.000-SCB	NBSD3-CD03A-AA
COMPACT CYLINDER, 1-1/2 BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24005D	FO-170.5	BRPSR-150-0.500-4	PSD4-0.500	SCC15-J-004	FP150x0.500-SCB	NBSD4-CD00I-AA
COMPACT CYLINDER, 1-1/2 BORE, 3/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C240075D	FO-170.75	BRPSR-150-0.750-4	PSD4-0.750	SCC15-J-006	FP150x0.750-SCB	NBSD4-CD00M-AA
COMPACT CYLINDER, 1-1/2 BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24010D	FO-171	BRPSR-150-1.000-4	PSD4-1.000	SCC15-J-010	FP150x1.000-SCB	NBSD4-CD01A-AA
COMPACT CYLINDER, 1-1/2 BORE, 1-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24015D	FO-171.5	BRPSR-150-1.500-4	PSD4-1.500	SCC15-J-014	FP150x1.500-SCB	NBSD4-CD01I-AA
COMPACT CYLINDER, 1-1/2 BORE, 2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24020D	FO-172	BRPSR-150-2.000-4	PSD4-2.000	SCC15-J-020	FP150x2.000-SCB	NBSD4-CD02A-AA
COMPACT CYLINDER, 1-1/2 BORE, 2-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24025D	FO-172.5	BRPSR-150-2.500-4	PSD4-2.500	SCC15-J-024	FP150x2.500-SCB	NBSD4-CD02I-AA
COMPACT CYLINDER, 1-1/2 BORE, 3 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24030D	FO-173	BRPSR-150-3.000-4	PSD4-3.000	SCC15-J-030	FP150x3.000-SCB	NBSD4-CD03A-AA
COMPACT CYLINDER, 1-1/2 BORE, 3-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24035D	FO-173.5	BRPSR-150-3.500-4	PSD4-3.500	SCC15-J-035	FP150x3.500-SCB	NBSD4-CD03I-AA
COMPACT CYLINDER, 1-1/2 BORE, 4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C24040D	FO-174	BRPSR-150-4.000-4	PSD4-4.000	SCC15-J-040	FP150x4.000-SCB	NBSD4-CD04A-AA
COMPACT CYLINDER, 2 IN. BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32005D	FO-310.5	BRPSR-200-0.500-4	PSD5-0.500	SCC20-J-004	FP200x0.500-SCB	NBSD5-CD00I-AA
COMPACT CYLINDER, 2 IN. BORE, 3/4 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C320075D	FO-310.75	BRPSR-200-0.750-4	PSD5-0.750	SCC20-J-006	FP200x0.750-SCB	NBSD5-CD00M-AA
COMPACT CYLINDER, 2 IN. BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32010D	FO-311	BRPSR-200-1.000-4	PSD5-1.000	SCC20-J-010	FP200x1.000-SCB	NBSD5-CD01A-AA
COMPACT CYLINDER, 2 IN. BORE, 1-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32015D	FO-311.5	BRPSR-200-1.500-4	PSD5-1.500	SCC20-J-014	FP200x1.500-SCB	NBSD5-CD01I-AA
COMPACT CYLINDER, 2 IN. BORE, 2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32020D	FO-312	BRPSR-200-2.000-4	PSD5-2.000	SCC20-J-020	FP200x2.000-SCB	NBSD5-CD02A-AA
COMPACT CYLINDER, 2 IN. BORE, 2-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32025D	FO-312.5	BRPSR-200-2.500-4	PSD5-2.500	SCC20-J-024	FP200x2.500-SCB	NBSD5-CD02I-AA
COMPACT CYLINDER, 2 IN. BORE, 3 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32030D	FO-313	BRPSR-200-3.000-4	PSD5-3.000	SCC20-J-030	FP200x3.000-SCB	NBSD5-CD03A-AA
COMPACT CYLINDER, 2 IN. BORE, 3-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C32035D	FO-313.5	BRPSR-200-3.500-4	PSD5-3.500	SCC20-J-035	FP200x3.500-SCB	NBSD5-CD03I-AA
COMPACT CYLINDER, 2-1/2 BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C40005D	FO-500.5	BRPSR-250-0.500-4	PSD6-0.500	SCC25-J-004	FP250x0.500-SCB	NBSD6-CD00I-AA
COMPACT CYLINDER, 2-1/2 BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C40010D	FO-501	BRPSR-250-1.000-4	PSD6-1.000	SCC25-J-010	FP250x1.000-SCB	NBSD6-CD00M-AA
COMPACT CYLINDER, 2-1/2 BORE, 2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C40020D	FO-502	BRPSR-250-2.000-4	PSD6-2.000	SCC25-J-025	FP250x2.000-SCB	NBSD6-CD02A-AA
COMPACT CYLINDER, 2-1/2 BORE, 2-1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C40025D	FO-502.5	BRPSR-250-2.500-4	PSD6-2.500	SCC25-J-024	FP250x2.500-SCB	NBSD6-CD02I-AA
COMPACT CYLINDER, 3 IN. BORE, 1/2 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C48005D	FO-700.5	BRPSR-300-0.500-4	PSD7-0.500	SCC30-J-004	FP300x0.500-SCB	NBSD7-CD00I-AA
COMPACT CYLINDER, 3 IN. BORE, 1 IN. STROKE, DOUBLE ACTING, THRU-HOLE MOUNT	C48010D	FO-701	BRPSR-300-1.000-4	PSD7-1.000	SCC30-J-010	FP300x1.000-SCB	NBSD7-CD00M-AA