



	Cutler-Hammer HT800	Description	Allen-Bradley 800T	Allen-Bradley 800H	Square D Type K	Siemens / Furnas Class 52	Siemens	GE CR104P Series	IDEC TWTD	ABB - CBF Line OLD	ABB-CBG Line NEW	Control Concepts		
	HT8		800T	800H	900	52S,52P,52N,52M, 52B,52A	3SB,P30	CR1,080	LSP,BST,ALD,NAL,A BD,APD,AYD,ASD,0 R,-L-1,IS,-NAK	CBF	CBK,CBG	AIP,APL,CBD,CBE,CBN,FVB,FV L,FVP,LPS,LPR,LPT,LRT,PBO,R LU,SRO,SSO,TFL,TFP		
163	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only	800T-J19	--	9001KS72FB	163	52SB2BCB	--	CR104PSM84B	163	--	CBF-S3SRL	CBG-M3SRL	SRORC-ASLWE
164	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS77FB	164	52SB2CCB		CR104PSM82B	164				
165	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS701FB	165			CR104PSM85B	165				
166	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS702FB	166			CR104PSM86B	166				
167	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS73FB	167				167				
168	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS74FB	168				168				
169	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS75FB	169				169				
170	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS76FB	170				170				
171	HT8JVH1D	3-Pos Sel Sw Blk Lever Spr Rtn Right Operator Only			9001KS79FB	171			CR104PSM83B	171				
172	HT8JVH1DAA5	3-Pos Sel Sw Black Lever Spring Return Right W/ 2NO	800T-J19A	--	--	172	52SB2CCBA1	--	CR104PSM84B91	172	ASD31L20N	CBF-S3SRL20	CBG-M3SRL20	SRORC-ASLWE-NO/NO
173	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only	800T-J91	800H-JR91	9001KS52B	173	52SA2BDB	3SB03-3BKB	CR104PSG94B	173	--	CBF-S3SK	CBG-M3SK	SRORC-ASHWE
174	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS57B	174	52SA2CDB		CR104PSG92B	174				
175	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS501B	175			CR104PSG95B	175				
176	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS502B	176			CR104PSG96B	176				
177	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS53B	177				177				
178	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS54B	178				178				
179	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS55B	179				179				
180	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS56B	180				180				
181	HT8JXH1D	3-Pos Sel Sw Blk Knob Spr Rtn Both Operator Only			9001KS59B	181			CR104PSG93B	181				
182	HT8JXH1DAA5	3-Position Sel Sw Black Knob Spring Return Both W/ 2NO	800T-J91A	800H-JR91A	--	182	52SA2CDBA1	--	CR104PSG94B91	182	ASD3320N	CBF-S3SK20	CBG-M3SK20	SRORC-ASHWE-NO/NO
183	HT8JXH1DAA5	3-Position Sel Sw Black Knob Spring Return Both W/ 2NO	800T-J91KT1A	800H-JR91KT1A		183				183				
184	HT8JXH1DAA5	3-Position Sel Sw Black Knob Spring Return Both W/ 2NO	800T-J91KT7A	800H-JR91KT7A		184				184				
185	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only	800T-J20	--	9001KS52FB	185	52SB2BDB	--	CR104PSM94B	185	--	CBF-S3SL	CBG-M3SL	SRORC-ASLWE
186	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS57FB	186	52SB2CDB		CR104PSM92B	186				
187	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS501FB	187			CR104PSM95B	187				
188	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS502FB	188			CR104PSM96B	188				
189	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS53FB	189				189				
190	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS54FB	190				190				
191	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS55FB	191				191				
192	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS56FB	192				192				
193	HT8JYH1D	3-Pos Sel Sw Blk Lever Spr Rtn Both Operator Only			9001KS59FB	193			CR104PSM93B	193				
194	HT8JYH1DAA5	3-Position Sel Sw Black Lever Spring Return Both W/ 2NO	800T-J20A	--	--	194	52SB2CDBA1	--	CR104PSM94B91	194	ASD33L20N	CBF-S3SL20	CBG-M3SL20	SRORC-ASLWE-NO/NO
195	HT8LAMPTOOL	Lamp/Bulb Removal Tool	--	800E-ALR1	--	195	--	--	--	195	OR-55	CBK-XLTL	--	LRT
196	HT8PP11	Standard Legend Marked "Up / Down"	--	800H-W039	--	196	52NL49	--	--	196	--	--	--	--
197	HT8PP5	Standard Legend Marked "On / Off"	--	--	--	197	--	P30LLS55	--	197	--	--	--	LPS-57
198	HT8PP8	Standard Legend Marked "Open / Close"	--	800H-W134	--	198	52NL34	P30LLS60	--	198	--	--	--	--
199	HT8RP79	Legend 70mm Round "Emergency Stop"	--	--	--	199	--	--	--	199	--	CBF-NPE30	CBG-NPE30	LPR-04
200	HT8SP13	Standard Legend Marked "Emerg. Stop"	800T-X504	800H-W372	9001KN205RP	200	52NL16	P30LLS27	--	200	NALD-104	CBF-NPE3	CBG-NPE3	LPS-04
201	HT8SP15	Standard Legend Marked "Forward"	800T-X508	800H-W105	9001KN206BP	201	52NL05	--	CR104PXN1BP011	201	NALD-106	CBF-NPE5	CBG-NPE5	LPS-07
202	HT8SP16	Standard Legend Marked "High"	800T-X512	800H-W107	9001KN214BP	202	52NL07	P30LLS24	CR104PXN1BP012	202	NALD-108	--	--	--
203	HT8SP17	Standard Legend Marked "In"	800T-X515	800H-W108	9001KN217BP	203	52NL21	P30LLS20	CR104PXN1BP013	203	NALD-109	CBF-NPE7	CBG-NPE7	--
204	HT8SP18	Standard Legend Marked "Inch"	800T-X516	800H-W109	9001KN216BP	204	--	P30LLS05	CR104PXN1BP014	204	NALD-110	CBF-NPE6	CBG-NPE6	LPS-09
205	HT8SP19	Standard Legend Marked "Jog"	800T-X517	800H-W110	9001KN218BP	205	52NL13	P30LLS28	CR104PXN1BP018	205	NALD-111	--	--	LPS-10
206	HT8SP20	Standard Legend Marked "Jog For."	800T-X518	800H-W111	9001KN219BP	206	--	--	CR104PXN1BP019	206	--	--	--	--
207	HT8SP21	Standard Legend Marked "Jog Rev."	800T-X519	800H-W112	9001KN220BP	207	--	--	CR104PXN1BP020	207	--	--	--	--
208	HT8SP22	Standard Legend Marked "Low"	800T-X524	800H-W113	9001KN215BP	208	52NL08	P30LLS25	CR104PXN1BP022	208	NALD-112	--	--	--
209	HT8SP23	Standard Legend Marked "Lower"	800T-X526	800H-W115	9001KN221BP	209	52NL20	--	CR104PXN1BP023	209	NALD-113	CBF-NPE9	CBG-NPE9	--
210	HT8SP24	Standard Legend Marked "Off"	800T-X527	800H-W116	9001KN204BP	210	52NL12	P30LLS02	CR104PXN1BP024	210	NALD-114	CBF-NPE10	CBG-NPE10	LPS-12
211	HT8SP25	Standard Legend Marked "On"	800T-X530	800H-W117	9001KN203BP	211	52NL11	P30LLS01	CR104PXN1BP025	211	NALD-115	CBF-NPE11	CBG-NPE11	LPS-13
212	HT8SP26	Standard Legend Marked "Open"	800T-X531	800H-W118	9001KN209BP	212	52NL17	P30LLS18	CR104PXN1BP026	212	NALD-116	CBF-NPE12	CBG-NPE12	LPS-14
213	HT8SP27	Standard Legend Marked "Out"	800T-X534	800H-W119	9001KN222BP	213	52NL22	P30LLS21	CR104PXN1BP027	213	NALD-117	--	--	--
214	HT8SP28	Standard Legend Marked "Raise"	800T-X535	800H-W120	9001KN227BP	214	52NL19	--	CR104PXN1BP028	214	NALD-118	CBF-NPE13	CBG-NPE13	--
215	HT8SP29	Standard Legend Marked "Reset"	800T-X538	800H-W121	9001KN223BP	215	52NL14	P30LLS15	CR104PXN1BP030	215	NALD-119	CBF-NPE14	CBG-NPE14	LPS-18
216	HT8SP30	Standard Legend Marked "Reverse"	800T-X539	800H-W122	9001KN207BP	216	52NL06	P30LLS08	CR104PXN1BP032	216	NALD-120	CBF-NPE15	CBG-NPE15	LPS-19
217	HT8SP31	Standard Legend Marked "Run"	800T-X540	800H-W123	9001KN224BP	217	52NL23	P30LLS06	CR104PXN1BP034	217	NALD-121	CBF-NPE16	CBG-NPE16	LPS-20
218	HT8SP32	Standard Legend Marked "Slow"	800T-X544	800H-W125	9001KN213BP	218	--	P30LLS11	CR104PXN1BP036	218	NALD-122	CBF-NPE18	CBG-NPE18	LPS-21
219	HT8SP33	Standard Legend Marked "Start"	800T-X547	800H-W126	9001KN201BP	219	52NL03	P30LLS03	CR104PXN1BP037	219	NALD-123	CBF-NPE19	CBG-NPE19	LPS-22
220	HT8SP34	Standard Legend Marked "Stop"	800T-X550	800H-W371	9001KN202BP	220	52NL04	P30LLS04	CR104PXN1BP040	220	NALD-125	CBF-NPE20	CBG-NPE20	LPS-23
221	HT8SP35	Standard Legend Marked "Up"	800T-X556	800H-W009	9001KN211BP	221	52NL09	P30LLS16	CR104PXN1BP047	221	NALD-127	CBF-NPE21	CBG-NPE21	LPS-25
222	HT8SP38	Standard Legend Marked "For. Rev."	800T-X566	800H-W132	--	222	52NL31	P30LLS57	--	222	NALD-205	CBF-NPE32	CBG-NPE32	--
223	HT8SP39	Standard Legend Marked "Hand Auto"	800T-X510	800H-W131	--	223	--	P30LLS52	CR104PXN1BP051	223	NALD-206	CBF-NPE22	CBG-NPE22	LPS-53
224	HT8SP40	Standard Legend Marked "High Low"	800T-X513	800H-W030	--	224	52NL30	--	CR104PXN1BP052	224	NALD-207	--	--	--
225	HT8SP41	Standard Legend Marked "Jog Run"	800T-X520	800H-W135	--	225	--	--	CR104PXN1BP053	225	NALD-208	CBF-NPE6	CBG-NPE23	--
226	HT8SP42	Standard Legend Marked "Off On"	800T-X622	800H-W133	--	226	52NL26	P30LLS50	CR104PXN1BP057	226	NALD-212	CBF-NPE24	CBG-NPE24	LPS-56
227	HT8SP43	Standard Legend Marked "Open Close"	800T-X532	800H-W134	--	227	--	--	CR104PXN1BP058	227	NALD-214	--	--	LPS-58
228	HT8SP44	Standard Legend Marked "Run Jog"	800T-X541	800H-W032	--	228	52NL29	P30LLS65	CR104PXN1BP061	228	NALD-217	--	--	LPS-60
229	HT8SP45	Standard Legend Marked "Safe Run"	800T-X542	800H-W033	--	229	52NL27	--	CR104PXN1BP062	229	NALD-218	--	--	--
230	HT8SP46	Standard Legend Marked "Start Jog"	800T-X548	800H-W138	--	230	52NL28	--	CR104PXN1BP087	230	--	--	--	--
231	HT8SP47	Standard Legend Marked "Start Stop"	800T-X549	800H-W137	--	231	52NL32	P30LLS56	CR104PXN1BP086	231	NALD-221	--	--	LPS-61
232	HT8SP48	Standard Legend Marked "Up Down"	800T-X557	--	--	232	--	--	CR104PXN1BP066	232	NALD-223	--	--	--
233	HT8SP49	Standard Legend Marked "Auto Off Hand"	800T-X501	800H-W154	--	233	--	--	CR104PXN1BP083	233	--	--	--	--
234	HT8SP50	Standard Legend Marked "For. Off Rev."	800T-X507	800H-W152	--	234	52NL38	--	CR104PXN1BP068	234	NALD-306	--	--	LPS-82
235	HT8SP51	Standard Legend Marked "Hand Off Auto"	800T-X511	800H-W151	--	235	52NL37	P30LLS80	CR104PXN1BP070	235	--	CBF-NPE26	CBG-NPE26	LPS-83
236	HT8SP53	Standard Legend Marked "Open Off Close"	800T-X533	800H-W153	--	236	52NL41	P30LLS88	CR104PXN1BP077	236	NALD-312	--	--	--
237	HT8SP54	Standard Legend Marked "Up Off Down"	800T-X558	800H-W160	--	237	52NL42	--	--	237	NALD-315	--	--	--
238	HT8SP67	Standard Legend Marked "Man. Auto"	--	800H-W031	--	238	52NL35	P30LLS58	--	238	NALD-211	CBF-NPE22	--	LPS-55
239	HT8SP68	Standard Legend Marked "Man. Off Auto"	800T-X625	800H-W062	--	239	--	P30LLS84	CR104PXN1BP076	239	--	CBF-E26	--	LPS-84
240	HT8SP69	Standard Legend Marked "For. Safe Rev."	--	--	--	240	--	--	--	240	--	--	--	--
241	HT8SP70	Standard Legend Marked "Run Safe Jog"	--	--	--	241	--	--	--	241	--	--	--	--
242	HT8SP71	Standard Legend Marked "On Stop Safe"	--	--	--	242	--	--	--	242	--	--	--	--
243	HT8SP73	Standard Legend Marked "Close"	800T-X502	800H-W101	9001KN208BP	243	52NL18	P30LLS19	CR104PXN1BP006	243	NALD-102	CBF-NPE1	CBG-NPE1	LPS-02
244	HT8SP74	Standard Legend Marked "Down"	800T-X503	800H-W102	9001KN210BP	244	52NL10	P30LLS17	CR104PXN1BP008	244	NALD-103	CBF-NPE2	CBG-NPE2	LPS-03
245	HT8SP75	Standard Legend Marked "Fast"	800T-X505	800H-W104	9001KN212BP	245	--	P30LLS09	CR104PXN1BP010	245	NALD-105	CBF-NPE4	CBG-NPE4	LPS-06
246	HT8SP76	Standard Legend Blank White/Silver Field	800T-X559	--	9001KN200SP	246	--	--	--	246	--	--	CBG-NPE28	--
247	HT8SP77	Standard Legend Blank Red/Black Field	800T-X621	--	9001KN200RP	247	--	--	CR104PXN1R	247	NALD-08	--	--	--
248	HT8SP80	Standard Legend Marked "Power On"	800T-X639	800H-W001	9001KN238BP	248	--	P30LLS30	CR104PXN1BP084	248	--	--	--	LPS-16
249	HT8SP81	Standard Legend Marked "Motor Run"	--	800H-W008	9001KN									