

CPU	Communication Interface	Connector type	K-Sequence	DirectNet (CCM2 or Host-link)		Modbus RTU		ASCII -Out Print Instruction
				Master	Slave	Master	Slave	
F1-130 series	RS-232C	RJ-12 (6-pin)	Yes	No	No	No	No	No
D2-230	RS-232C	RJ-12 (6-pin)	Yes	No	No	No	No	No
D2-240 Port 1	RS-232C	RJ-12 (6-pin)	Yes	No	No	No(1)	No(1)	No
D2-240 Port 2	RS-232C	RJ-12 (6-pin)	Yes	No(1)	Yes	No(1)	No(1)	No
D2-250 Port 1	RS-232C	RJ-12 (6-pin)	Yes	No(1)	Yes	No(1)	No(1)	No
D2-250 Port 2	RS-232C/422	15 pin SVGA	Yes	Yes	Yes	Yes	Yes	Yes
D2-RSSS Slice	RS-232C	RJ-12 (6-pin)	Yes	No	Yes	No	No	No
D3-330/330P	RS-232C/422 with DCU	25-Pin D shell	No	No	No	No	No	No
D3-340 Port 1	RS-232C	RJ-11 (4 pin)	No	No	Yes	No	Yes	No
D3-340 Port 2	RS-232C	RJ-11 (4 pin)	No	Yes	Yes	No	Yes	No
D3-350 Port 1	RS-232C	RJ-12 (6 pin)	Yes	No(1)	Yes	No	No(1)	No(1)
D3-350 Port 2	RS-232C/422	25 Pin D shell	Yes	Yes	Yes	Yes	Yes	Yes
D4-430 Port 0	RS-232C	15 Pin D shell	Yes	No(1)	No(1)	No(1)	No(1)	No
D4-430 Port 1	RS-232C/422	25 Pin D shell	Yes	No(1)	Yes	No(1)	No(1)	No(1)
D4-440 Port 0	RS-232C	15 Pin D shell	Yes	No(1)	No(1)	No(1)	No(1)	No(1)
D4-440 Port 1	RS-232C/422	25 Pin D shell	Yes	No(1)	Yes	No(1)	No(1)	No(1)
D4-450 Port 0	RS-232C	15 Pin D shell	Yes	No(1)	No(1)	No(1)	No(1)	No(1)
D4-450 Port 1	RS-232C/422	25 Pin D shell	Yes	Yes	Yes	Yes	Yes	Yes
D4-450 Port 2	RS-232C	RJ-12 (6-pin)	Yes	Yes	Yes	No(1)	No(1)	Yes
D4-450 Port 3	RS-422	25 Pin D shell	Yes	Yes	Yes	Yes	Yes	Yes
D4-Slice port		15 Pin D shell	Yes	No	No	No	No	No

(1) A module is available that supports this protocol or interface.

Module	Communication Interface	Connector type	K-Sequence	DirectNet (CCM2 or Host-link)		Modbus RTU		ASCII And other Protocols. See Manual
				Master	Slave	Master	Slave	
D2-DCM	RS-232C/422	25 Pin D shell	Yes/slave	Yes	Yes	No	Yes	No
D2-ECOM	Ethernet 10base-T	RJ-45	Yes	Yes	Yes	No	No	No
D3-DCM	RS-232C/422	RJ-12 (6-pin)	Yes	Yes	Yes	No	Yes	No
D3-232-DCU	RS-232C	25 Pin D shell	No	No	Yes	No	No	No
D3-422-DCU	RS-422	25 Pin D shell	No	No	Yes	No	No	No
D4-DCM	RS-232C/422	25 Pin D shell	Yes/slave	Yes	Yes	No	Yes	No
D4-ECOM	Ethernet 10base-T	RJ-45	Yes	Yes	Yes	No	No	No
F4-MAS-MB	RS232/422/485	9 pin D shell	No	No	No	Yes	No	Yes
F4-SLV-MSB	RS232/422/485	9 pin D shell	No	No	No	No	Yes	Yes
F4-SLV-TW	RS232/422/485	9 pin D shell	No	No	No	No	No	Yes
F4-CP128-1 F4-CP512 F4-CP128-T	RS232/422/485	9 pin D shell	See manual	See manual	See manual	See manual	See manual	Yes
F4-SDN	RS-485	9 Pin D shell	No	No	No	No	No	Yes